



BC CYTOFLEX LX (VSSC template)

LASER	channel position	Band-Pass Filter	EXAMPLE
488	1	488	Side Scatter
	2	525/40	FITC / AF488 / eGFP / YFP
	3	610/20	PE-TxRed / ECD / PI*
	3	690/50	PerCP / PerCP-Cy5.5 / PI* / 7AAD
561	5	610/20	PE-TxRed / ECD / PI* / Cychrome / m-Cherry
	8	763/43	PE-Cy7
	4	585/42	PE / TRITC / DSRed(RFP) / tdTomato
	6	675/30	PECy5
	7	710/50	PECy5.5
640	9	660/10	APC / Alexa 647/Cy5
	10	712/25	Alexa 700
	11	763/43	APC-Cy7 / APC-H7 / Alexa 780
405	nn	405	VSSC
	12	450/45	Pacific Blue / Cas.Blue / CFP / DAPI / V450
	13	525/40	AmCyan / Pacific Orange / Cas.Yellow / V500
	14	610/20	BV605 / QDot605
	15	660/10	BV650 /Qdot665
355	16	405/30	BUV395
	17	525//40	BUV496 / Hoechst-Red
	18	740/35	BUV740
808	19	885/40	PF840
	20	840/20	AF790 / CF790