



## BD FACSARIA FUSION

Laser	Position of PMT	Filter	Band-Pass	Fluorochrome (Example)
488	C	488/10	Blank	SSC
	B	B 530/30	502 LP	FITC / GFP/ Alexa Fluor 488 / BB515 / VioBright 516 / YFP
	A	B 695/40	655 LP	PerCP / PerCP Cy5.5 / 7AAD
561	E	Y 582/15	Blank	PE / dTomato / mOrange / DS Red (RFP) / TRITC
	D	Y 610/20	600 LP	PI / ECD / mCherry / PE-Vio 615 / PE TxRed / Cychrome
	C	Y 670/14	630 LP	PE Cy5 / 7AAD
	B	Y 710/50	685 LP	PE Cy5.5
	A	Y 780/60	735 LP	PE Cy7 / PE-Vio770
640	C	R 670/30	Blank	APC / Alexa Fluor 647 / Cy5
	B	R 730/45	690 LP	APC Cy5.5 / APC R700 / Alexa Fluor 700
	A	R 780/60	755 LP	APC Cy7 / APC H7 / APC Alexa 750 / APC-Vio770 / Alexa 780
405	F	V 450/50	Blank	Pacific Blue / V450 / BV 421 / BFP / VioBlue / Casc. Blue / CFP / DAPI
	E	V 525/50	505 LP	Krome Orange / Pacific Orange / AmCyan / V500 / BV 510 / VioGreen / Casc. Yellow
	D	V 610/20	595 LP	BV 605 / Qdot 605
	C	V 660/20	630 LP	BV 650
	B	V 710/50	690 LP	BV 711
	A	V 780/60	750 LP	BV 786 / Qdot 800